

Tetron Tape for Temporary Vessel Ligation

TETRON TAPE





Vessel wall damage is frequently observed when forceps are used for vessel ligation. This tape was developed to resolve the problem by reducing damage while achieving simple stump ligation by tape distinction.

Color	Pink, Blue, Green, Yellow, Undyed
Width	2mm, 3mm, 4mm, 5mm

□ Tetron Tape with Needle

Uterine Cervix Ligation

Needle Size	Width	Length	Quantity	Color	Item Code
G Blunt Point 1/2 Circle					
 G-40 mm (McDonald)	3mm	50cm (20in)	1pc/pkg ×20	Undyed	XG003
H Blunt Point 3/8 Circle					
 H-45 mm (Shirodkar)	3mm	50cm (20in)	1pc/pkg ×20	Undyed	XH003

Non-sterile

Length	Quantity	Color	Width			
			2mm	3mm	4mm	5mm
5m (16ft5in)	1spool/pkg	Pink	2TR05	3TR05	4TR05	5TR05
		Blue	2TB05	3TB05	4TB05	5TB05
		Green	2TG05	3TG05	4TG05	5TG05
		Yellow	2TY05	3TY05	4TY05	5TY05
		Undyed	2TW05	3TW05	4TW05	5TW05
10m (32ft10in)	1spool/pkg	Pink	2TR10	3TR10	4TR10	5TR10
		Blue	2TB10	3TB10	4TB10	5TB10
		Green	2TG10	3TG10	4TG10	5TG10
		Yellow	2TY10	3TY10	4TY10	5TY10
		Undyed	2TW10	3TW10	4TW10	5TW10
25m (82ft)	1spool/pkg	Pink	2TR25	3TR25	4TR25	5TR25
		Blue	2TB25	3TB25	4TB25	5TB25
		Green	2TG25	3TG25	4TG25	5TG25
		Yellow	2TY25	3TY25	4TY25	5TY25
		Undyed	2TW25	3TW25	4TW25	5TW25

Sterile

Length	Quantity	Color	Width			
			2mm	3mm	4mm	5mm
40cm (16in)	1ps/pkg × 10pkg/pack	Pink	2T40R	3T40R	4T40R	5T40R
		Blue	2T40B	3T40B	4T40B	5T40B
		Green	2T40G	3T40G	4T40G	5T40G
		Yellow	2T40Y	3T40Y	4T40Y	5T40Y
		Undyed	2T40W	3T40W	4T40W	5T40W
45cm (18in)	1ps/pkg × 10pkg/pack	Pink	2T45R	3T45R	4T45R	5T45R
		Blue	2T45B	3T45B	4T45B	5T45B
		Green	2T45G	3T45G	4T45G	5T45G
		Yellow	2T45Y	3T45Y	4T45Y	5T45Y
		Undyed	2T45W	3T45W	4T45W	5T45W
50cm (20in)	1ps/pkg × 10pkg/pack	Pink	2T50R	3T50R	4T50R	5T50R
		Blue	2T50B	3T50B	4T50B	5T50B
		Green	2T50G	3T50G	4T50G	5T50G
		Yellow	2T50Y	3T50Y	4T50Y	5T50Y
		Undyed	2T50W	3T50W	4T50W	5T50W
60cm (24in)	1ps/pkg × 10pkg/pack	Pink	2T60R	3T60R	4T60R	5T60R
		Blue	2T60B	3T60B	4T60B	5T60B
		Green	2T60G	3T60G	4T60G	5T60G
		Yellow	2T60Y	3T60Y	4T60Y	5T60Y
		Undyed	2T60W	3T60W	4T60W	5T60W